

INTRANEWS

Volume 1, Issue 3, May 2006

PRODUCT PREVIEW

New Straight Abutments

Advantages:

- Two NEW Collar heights; 1mm and 3mm
- Optimally machined chamfer.
- Screw Retained Abutment = INDEXability
- Platform Switching concept




IAA01 on Long Collar Implant

IAA03 on Short Collar Implant

Four new straight abutments complement Intralock's Prosthetic Component family. They feature a machined chamfer designed to make it easier for technicians to wax up anatomically correct margins with equally correct emergence profiles. The chamfers are especially helpful when fabricating all ceramic crowns, i.e. Empress, Procera, etc...

The abutment margins close slightly short of the implant platform limit, positioning the prosthetic connection away from the bone enhancing crestal bone preservation. You can also choose between collar heights of 1mm or 3mm. This combination guarantees margins below tissue level and afford optimal esthetics with minimal lab or chairside reworking of the abutments.

The Wide Abutments not only have a wider diameter at the margin level, but also on the abutment body itself. This permits more space for drilling parallelism corrections if needed, and once the abutment is cemented, ensures greater crown retention.



Close-up of abutment margins